


# ReMarcoble truths

Why are Marco auto refractors rated first for accuracy and ease of use across the most extensive line of refraction systems?

## It's Our Unique Technology.

- /// Super Luminescent Diode technology makes it possible to now accurately measure patients with cataracts, corneal opacity, IOLs and post Lasik
- /// Zonal Ring Image Method measures auto refraction at the largest possible pupil size up to 4mm for greater correlation to your subjective refraction
- /// Automatic 3-D eye tracking, aligning, and focusing insures the most reliable and repeatable refraction and keratometry readings
- /// Automatic Acquisition eliminates user subjective interpretation of when to take the readings. Guaranties consistent measurements.
- /// Peripheral Keratometry with sagittal radius and eccentricity values for corneal evaluations, contact lens fitting, and refractive surgery
- /// Cornea and Pupil size measurements

To experience the benefits of the most accurate autorefractor on the market please contact us to schedule your free practice consultation.



Marco certifies communication with most EMR companies.

The Difference  is Marco™

